



MSR Gold™ FastFit

MSR Gold™ 1500/2 FastFit

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ 1200 FastFit can be operated in a lamp wattage range between 800W and 1400W.

Product data

GeniPubl	
PGJX50 PGJX50	PGJX50 [PGJX50]
Universal Universal	Universal [Universal]
Entertainment	Entertainment
750 h	750 h
FastFit	FastFit
LittPubl	
104000 lm	104000 lm
116000 lm	116000 lm
302	302
320	320
7200 K	7200 K
77 lm/W	77 lm/W
77	77

ElecPubl	
1500 W	1500 W
16.1 A	16.1 A
198 V	198 V
CntrPubl	
Yes	Yes
MechPubl	
PGJX50	PGJX50
LDRPubl	
950 °C	950 °C
500 °C	500 °C
ProductPubl	
MSR Gold™ 1500/2 FastFit	MSR Gold™ 1500/2 FastFit


MSR Gold™ FastFit

8718699625955	8718699625955
343350	343350
1	1
4	4

928410305115	928410305115
0.133 kg	0.133 kg

Warnings and Safety


Dimensional drawing




MSR Gold 1500/2 FastFit

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 1500/2 FastFit	28 mm	6.3 mm	64 mm	66 mm	65 mm	128 mm	50 mm

Photometric data



Spectrum MSR Gold™ 1500 FastFit



Spectrum MSR Gold™ 1500 FastFit

